

PhlatLight® LED Development Kit Product Brief

DK-114N Series



Overview

PhlatLight DK-114N series development kits are a comprehensive solution designed specifically to support development of PhlatLight LED based solutions. The kit includes high-current drivers, efficient thermal management solutions, clean interfaces, and cabling for use with standard laboratory equipment. The inclusion of these components ensures PhlatLight LEDs can be operated optimally at any drive condition. Whether this is low power for maximum efficiency, high power for maximum brightness or anywhere in between, the PhlatLight DK-114N Development Kit ensures the right performance.

This plug and play solution can easily be connected to standard laboratory equipment through standard connectors and allows system designers to save weeks in their development cycles.

Key Features

- Compatibility with all CBT and PT series PhlatLight products, with optimization for devices with an emitting area less than 9mm^2
- Driver board supply currents of 14A with overdrive currents up to 17A
- Available in a single channel or three channel versions

Main Features

- Driver circuitry based off of the National Semiconductor LM3433 IC
- Can be operated either in pulsed or continuous waveform (CW) modes
- Static current control via on board dial knob
- Optional dynamic current control by user-supplied external device
- Pulse width modulation input supports pulsed mode operation with duty cycle ranging from 0% - 100%
- Pulse frequencies greater than 40kHz supported
- Fast rise and fall times - less than 1 microsecond
- Fast current level switching - less than 5 microseconds
- Typical thermal resistance of $0.6\text{ }^{\circ}\text{C/W}$ from heat sink to ambient
- Grounded common anode configuration - no electrical isolation between multiple devices is required

PhlatLight Evaluation Kit Contents

- 1 or 3 driver cards capable of providing 14A
- 1 or 3 compact, high performance, air-cooled heat sinks.
- Clean interface board
- Electrical wiring between all boards and PhlatLight devices
- Thermal interface materials and mounting hardware
- User manual including step-by-step instructions for set-up and operation of the kit.

User Equipment Required

- Standard 12V laboratory power supply.
- Standard instrumentation - volt meter, oscilloscope, photodetector.
- Pulse generator for PWM dimming

Note: PhlatLight LED products are not included in the development kits and must be purchased separately.

Product Compatibility

Development Kit Part Number	Compatible PhlatLight LEDs
DK-114N-1, DK-114N-3	CBT-40 [*] , CBT-90 [*] , CST-90 [*] , SSR-90 [*] , CBT-120 [†] PT-39 [*] , PT-54 [*] , PT-85 [†] , PT-120 [†]

*Note *:* Recommended product for optimal use

Note †: Product can be used, but not operated at full power

Ordering Information

Ordering Part Number	Product	Description
DK-114N-1	DK-114N PhlatLight Development Kit, Single Channel	Single channel development kit, with 14A driver board, heat sink, interface board, cable assemblies and user manual
DK-114N-3	DK-114N PhlatLight Development Kit, Triple Channel	Three channel development kit, with 14A driver board, heat sink, interface board, cable assemblies and user manual

The products, their specifications and other information appearing in this document are subject to change by Luminus Devices without notice. Luminus Devices assumes no liability for errors that may appear in this document, and no liability otherwise arising from the application or use of the product or information contained herein. None of the information provided herein should be considered to be a representation of the fitness or suitability of the product for any particular application or as any other form of warranty. Luminus Devices' product warranties are limited to only such warranties as accompany a purchase contract or purchase order for such products. Nothing herein is to be construed as constituting an additional warranty. No information contained in this publication may be considered as a waiver by Luminus Devices of any intellectual property rights that Luminus Devices may have in such information. PhlatLight[®] is a registered trademark of Luminus Devices, Inc., all rights reserved.

Luminus Devices
1100 Technology Park Drive
Billerica, MA 01821

E-mail: sales@luminus.com

978-528-8000 (T)
978-528-8001 (F)

www.luminus.com

AMEYA360

Components Supply Platform

Authorized Distribution Brand :



Website :

Welcome to visit www.ameya360.com

Contact Us :

➤ Address :

401 Building No.5, JiuGe Business Center, Lane 2301, Yishan Rd
Minhang District, Shanghai , China

➤ Sales :

Direct +86 (21) 6401-6692
Email amall@ameya360.com
QQ 800077892
Skype ameyasales1 ameyasales2

➤ Customer Service :

Email service@ameya360.com

➤ Partnership :

Tel +86 (21) 64016692-8333
Email mkt@ameya360.com