

Reduce risk of carpal tunnel syndrome!

Heyco® Lockit™ Strain Relief Pre-Assembly Equipment

Pre-Assembly Equipment for Heyco Assembly-Friendly Lockit Series Strain Reliefs:

RDD Lockits – for “Double D” and Round Mounting Holes.

ST Lockits – for Rectangular Mounting Holes.

Pre-Assemble Lockits onto cable for faster final assembly!

Watch this equipment in action at www.Heyco.com

Click on our Strain Relief Bushings Section and then the video

“Evolution of the Heyco Strain Relief Bushing” in the upper left square.



A

A Headlock™ for RDD and ST Lockits


Assembly head for RDD and ST Lockit Strain Reliefs. Simply place a Lockit Strain Relief into the “U” opening of the assembly head. Then place the cable into the bushing body and close the head to secure the Lockit™ Strain Relief permanently onto the wire. This completed sub-assembly can then be installed with fingertip pressure into the application’s mounting hole—at a later time, in a different place, for lower installed cost!



B

B FootLock™

Assembly machine for RDD and ST Lockit Strain Reliefs. This foot-pedal activated assembly machine is identical to Autolock™, except that the gravity fed track is loaded by hand instead of by a vibratory bowl.



C

C Autolock™ Semi-Automatic

Assembly machine for RDD and ST Lockit Strain Reliefs. Suitable for high volume production runs where batched sub-assemblies are desirable. Includes vibratory feeder bowl, track and head. The operator simply inserts the cable into the assembly head slot, then presses the foot pedal to secure the Strain Relief permanently onto the wire. This completed sub-assembly can be installed with fingertip pressure into the application’s mounting hole—at a later time, in a different place, for lower installed cost!

Equipment for European requirements (motor power ratings and shielding) available, consult Heyco.

For Lockit Strain Relief Hand Pliers see page 4-6.

Heyco® Lockit™ Strain Relief Pre-Assembly Equipment Directory



TO ASSEMBLE Lockit™ Strain Relief Series	Catalog Page Ref.	Hand Pliers	USE THE FOLLOWING PART NOS.			
			A Headlock	B Footlock	C Autolock	C† Eurolock

RDD Lockits

RDD 100, RDD 100A	4-13	0026	ST16	ST14, ST14E†	ST13	ST13E
RDD 101, RDD 101A	4-9					
RDD 100-90, RDD 100A-90	4-16					
RDD 101-90, RDD 101A-90	4-15	0026	*	*	*	*
RDD 100-7, RDD 100A-7	4-14					
RDD 101-7	4-14					
RDD 200, RDD 200-2	4-13					
RDD 201, RDD 201-2	4-10	0027	ST17	ST19	ST18	*
RDD 301, RDD 301-2	4-10					
RDD 401	4-10					
RDD 200-90	4-16					
RDD 201-90	4-15	0027	ST17-90	ST19-90	*	*
RDD 301-90	4-15					
RDD 501	4-11	**	ST20	ST27	ST26	*
RDD 510	4-13					
RDD 601	4-11	**	ST31	ST34	*	*
RDD 6N-2	4-9	**	ST32	ST33	*	*

ST Lockits

ST 100L	4-8	0023	ST12	ST11	ST10	*
ST 100N	4-8	0020	OST1	OST4	OST3	OST3E
ST 101N	4-7					
ST 101A	4-17	0025	ST15	OST0	OST6	*
ST 200N	4-8	0073	OST7	OST9	OST8	*
ST 201N, ST 301N	4-7					


† ST14E guarding meets European standards.

Eurolock **ST13E** and **OST3E** have a 230V 50/60 Hz rated motor.


*Consult Heyco for availability.

**Headlock, Footlock or Autolock required due to cable thickness.


To use Hand Pliers with
Lockit™ Strain Reliefs:




Position on Wire



Squeeze Pliers



Push into Double D (RDD)
or Rectangular (ST)
Mounting Hole



or Set Aside for Future
Final Assembly



Part No. 0020
(R 100)

AMEYA360

Components Supply Platform

Authorized Distribution Brand :



Website :

Welcome to visit www.ameya360.com

Contact Us :

➤ Address :

401 Building No.5, JiuGe Business Center, Lane 2301, Yishan Rd
Minhang District, Shanghai , China

➤ Sales :

Direct +86 (21) 6401-6692

Email amall@ameya360.com

QQ 800077892

Skype ameyasales1 ameyasales2

➤ Customer Service :

Email service@ameya360.com

➤ Partnership :

Tel +86 (21) 64016692-8333

Email mkt@ameya360.com